



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/14/21	GUTTADAURO



**NOTES**

**MATERIAL:**  
MOLDED HOOD: THERMOPLASTIC POLYURETHANE, BLACK  
INSULATOR: NYLON, BLACK  
SHELL/SCREW NUT: BRASS, NICKEL PLATE  
CONTACTS: PHOSPHOR BRONZE, 15µ" MIN. GOLD PLATE


**ELECTRICAL:**  
NOMINAL VOLTAGE RATING: 250 VAC/VDC  
MAX CURRENT: 4A

**APPLICATION:**  
INGRESS PROTECTION RATING IS IP68 (MATED).

**ENVIRONMENTAL:**  
OPERATING TEMPERATURE RANGE: -40°C TO +80°C  
CABLE JACKET RESISTANCE: OIL, SUNLIGHT, AND WELD SPLATTER RESISTANT  
CABLE FLEX LIFE: 1 MILLION CYCLE TEST (10X CABLE OD)  
10 MILLION CYCLE TEST (20X CABLE OD)

**MISCELLANEOUS**  
CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY  
CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

PART NUMBER	LENGTH	
	METERS	FEET
TRG503-T4T-05M	0.5	1.64
TRG503-T4T-3M	3.0	9.84
TRG503-T4T-5M	5.0	16.41

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [.5]   ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY BZHANG	10/10/21		CATEGORY <b>TELECOM/MODULAR</b> PRODUCT DESCRIPTION <b>C5e M12 4PD SF/UTP IND-OD-HF, M12F/M12F</b>
	CHECKED BY SPAN	10/10/21		
	APPROVED BY GUTTADAURO	10/10/21		
THIRD-ANGLE PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>   CAGE CODE <b>43321</b>   DWG. NO. <b>TRG503-T4T</b>   REV. <b>A</b> SCALE: NONE   CAD FILE: TRG503-T4T.SLDDRW   SHEET 1 OF 1	