


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/4/22	JJOHNSTON



PART NUMBER	LENGTH METERS [FEET]
FCA-MMS108D90P	0.5 [1.64]
FCA-MMS108D91P	1.0 [3.28]


WIRING MAP	
MPO FIBER #	COLOR
1	N/A
2	N/A
3	BLUE
4	ORANGE
5	GREEN
6	BROWN
7	GREY
8	WHITE
9	RED
10	BLACK
11	N/A
12	N/A

NOTES:

1. SC CONNECTOR ASSEMBLY POLISH TYPE: UPC
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 an INFINITI® brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY DMAY		1/24/22			CATEGORY	FIBER OPTICS
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [.5] ± 1/32 .XXX = ± .005 [.13] ANGLES ± 1°		CHECKED BY DFRISIello		1/28/22				
THIRD-ANGLE PROJECTION 		APPROVED BY JJOHNSTON		2/4/22				
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION PATCH CORD SM OS2 8CORES MPO(MALE, STANDARD LOSS)-SC/UPC 0.9mm PVC 8COLOUR		SIZE		CAGE CODE	ITEM NO.	REV.
COLOR VARIATIONS MAY OCCUR		A		43321		FCA-MMS108D9		A
SCALE: NONE		CAD FILE: FCA-MMS108D9.SLDDRW		SHEET 1 OF 1				