

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300390385

Status:

Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

Micro-Change Terminator, Female with Resistor, 5 Pole



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Field Attachable / Accessories
Series	130039
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Taxonomy	Circular Industrial Connectors
Type	Terminator
UPC	78678830952
Physical	
Cable Diameter	N/A
Coupling Type	Internal Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	Single
Material - Connector Body	Polyamide
Material - Coupling Nut	Die-Cast Zinc
Material - Plating Mating	Gold
Net Weight	1.240/g
Orientation	Straight
Poles	5
Temperature Range - Operating	0°C to +60°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	30V
Material Info	
Engineering Number	DND150
Reference - Drawing Numbers	
Sales Drawing	SD-130039-012-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained
ZZCERT_CE - Declaration of Conformity	CER_4000409978_00_000.pdf
ZZCERT_UKCA - Declaration of Conformity	CER_4000410292_00_000.pdf

Search Parts in this Series

130039 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION