

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300700019](#)
Status: **Active**
Overview: BradPower Cordsets and Receptacles
Description: BradPower D-Size (1 3/8"-M35) Female Closure Cap, Internal Threads, 38.35mm Diameter

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|--------------------|---|
| Product Family | Field Attachable / Accessories |
| Series | 130070 |
| IP Rating | N/A |
| Material - Contact | N/A |
| Overview | <u>BradPower Cordsets and Receptacles</u> |
| Product Name | BradPower D-Size |
| Taxonomy | Industrial Accessories |
| Type | Accessory - Closure Cap |
| UPC | 78678855155 |

Physical

| | |
|-------------------------------|-------------------|
| Cable Diameter | N/A |
| Coupling Type | N/A |
| Diagnostics / LEDs | No |
| Diagnostics Port | No |
| Gender | N/A |
| Keyway | N/A |
| Material - Connector Body | Anodized Aluminum |
| Material - Coupling Nut | N/A |
| Material - Plating Mating | n/a |
| Net Weight | 98.110/g |
| Orientation | N/A |
| Poles | N/A |
| Temperature Range - Operating | -20°C to +90°C |
| Wire Size AWG | N/A |

Electrical

| | |
|-------------------------------|-----|
| Current - Maximum per Contact | N/A |
| Voltage - Maximum | N/A |

Material Info

| | |
|--------------------|---------|
| Engineering Number | 55-0298 |
|--------------------|---------|

Reference - Drawing Numbers

| | |
|---------------|-------------------|
| Sales Drawing | SD-130070-005-001 |
|---------------|-------------------|



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[130070 Series](#)