

## Han 24HPR-Compact-HSE-HC-for CL-M40



Image is for illustration purposes only. Please refer to product description.

Part number	19 40 524 0583
Specification	Han 24HPR-Compact-HSE-HC-for CL-M40
HARTING eCatalogue	<a href="https://b2b.harting.com/19405240583">https://b2b.harting.com/19405240583</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> HPR Compact
Type of hood/housing	Hood
Type	High construction

### Version

Size	24 HPR
Version	Side entry
Cable entry	1x M40
Locking type	Central locking lever
Field of application	Hoods/housings for harsh outdoor environments

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68 IP6K9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated



Pushing Performance  
Since 1945

## Material properties

Colour (hood/housing)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
CE	Yes

## Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors