

3ft (1m) Premium Certified HDMI 2.0 Cable with Ethernet - Durable High Speed UHD 4K 60Hz HDR
- Rugged M/M HDMI Cord with Aramid Fiber - TPE - Ultra HD Monitors, TVs & Displays

Product ID: RHDMM1MP



This 3 ft. (1 m) High Speed HDMI Cable with Ethernet withstands the daily demands of connecting your HDMI devices. Tested to endure strenuous wear and tear, the rugged cable is a must-have for both business and consumer applications.

The HDMI Premium Certified cable has aramid fiber reinforcement that braces it from the stress of frequent bends from hooking up your TV or monitor. This also lets the cord flex without over-stretching or damaging the core of the cable.

- Aramid fiber adds strength and durability to the cable
- Insulated conductors reduce friction, provide more flexibility
- EMI protection with aluminum-mylar foil with braided shielding
- TPE cable jacket is more flexible than a standard PVC cable

The high quality cable is constructed to prevent the connector from separating from the jacket. The extra-long strain relief molding is tested to withstand over 10,000+ bend cycles at a 180 angle.

- HDMI gold plated connector with metal shield protects the circuit board from EMI and reinforces the connection point
- Strain relief tested to tolerate over 10,000+ bend cycles at a 180 angle

Supporting all HDMI 2.0 specifications, this HDMI Premium Certified adapter cable supports resolutions up to 4K 60Hz with a bandwidth of up to 18Gbps. The HDMI cable also supports HDR for higher contrast ratio and vivid colors

providing an enriched and enjoyable viewing experience.

RHDMM1MP is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect 4K/Ultra HD displays and devices

Features

- **HIGH PERFORMANCE CABLE:** 3.3 ft (1 m) Premium Certified HDMI 2.0 with Ethernet, 4K 60Hz (up to 4096x2160p), 18Gbps bandwidth, HDR10 for high contrast ratio, Ultra wide aspect ratio, 32 Ch multi-stream audio (5.1/7.1/DD+/Dolby TrueHD/Atmos) 1536Hz sampling
- **DURABLE:** HDMI cable w/aramid fiber for high tensile strength & durability; Tested up to 10000+ bend cycles at 180 angle & 5000+ insertions; Al-Mylar Foil w/ Braid provides EMI shielding ensures signal integrity; Ideal for Commercial environments
- **FLEXIBLE CABLE:** Long lasting TPE jacket and strain relief absorbs stress of frequent bends protecting the core of the rugged UHD HDMI 34AWG cord; TPE is non-toxic, halogen free and RoHS certified for environmental sustainability
- **APPLICATIONS:** Ideal for home/office and travel, works with computer/laptop/desktop/workstation; Connect your TV/monitor/display/projector/soundbar; Samsung/Sony/Apple TV/Dell/LG; Compatible with HDMI 2.0 Ultra HD, 1080p Full HD and previous HDMI versions
- **SPECS:** 1 m (3.3 ft) Black HDMI 2.0 HDMI Male to Male 34 AWG Reinforcement: Aramid Fiber Jacket: TPE EMI Shielding Audio Return Channel (ARC), HDCP 2.2, CEC, BT.2020 colorimetry Lifetime Warranty

Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Audio Specifications	Up to 32 audio channels with 1536Hz sampling rate
----------------------	---

Connector(s)

Connector A	1 - HDMI (19 pin)
	1 - HDMI (19 pin)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	30 AWG
Cable Length	3.3 ft [1 m]
Product Length	3.3 ft [1.0 m]
Product Width	0.7 in [1.7 cm]
Product Height	0.2 in [5 mm]
Weight of Product	1.2 oz [33 g]

Packaging Information

Package Quantity	1
Package Length	5.9 in [15 cm]
Package Width	0.8 in [2 cm]
Package Height	8.1 in [20.5 cm]
Shipping (Package) Weight	2.9 oz [82 g]

What's in the Box

Included in Package	1 - HDMI Cable
---------------------	----------------

**Product appearance and specifications are subject to change without notice.*

