

20in (50cm) USB A to C Charging Cable, Coiled Heavy Duty Fast Charge & Sync, High Quality USB 2.0 A to USB Type-C Cable, Rugged Aramid Fiber, Durable Male to Male USB Cable

Product ID: R2ACC-50C-USB-CABLE



This 20in (50cm) coiled USB A to USB C cable can withstand the daily demands of charging and syncing your mobile devices. It contracts to 12in (32cm) making it compact and convenient to store.

The durable USB A to USB C charging cable has aramid fiber reinforcement that shelters it from the stress of frequent bends. This also lets the cable flex without over-stretching or damaging the core of the cable.

The USB A to USB C cable is constructed to prevent the connector from separating from the jacket. The extra-long strain relief molding is tested to withstand over 5,000+ bend cycles at a 180 angle.

The durable cable supports all USB 2.0 specifications providing a dependable connection for all your USB-C devices. It supports up to 3A for charging your USB C compatible devices.

R2ACC-50C-USB-CABLE is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility





Applications

Features

• USB A TO C CHARGING CABLE: Coiling cable stretches up to 20in (50cm) and contracts to 12.5in (32cm)



preventing it from being tangled; Strong but soft flexible TPE jacket, makes it easy to coil and put away in vehicle console or glove compartment

- RUGGED DESIGN: USB A to USB Type-C cable reinforced with aramid fiber for increased tensile strength; Tested to withstand 10000+ insertions & 5000+ bend cycles at 180 angle; Durable TPE jacket and strain relief; TPE is non-toxic, halogen free
- FAST CHARGE AND SYNC: Supporting up to 3A for fast charging from a USB-A port or Quick Charge power adapter, this high quality cord is designed to charge and sync your USB C devices
- USB-C COMPATIBILITY: Heavy duty data transfer cable allows you to charge and sync your USB Type C devices including your iPad Pro, iPad Mini, Samsung Galaxy S8, S9, S10, S20, S20+, One Plus & Google Pixel 3a, 3, 4, 5, 6 series
- SPECS: Length: 20in (50cm) Color: Black Cable Type: Coiled Connectors: USB-C to USB-A Performance: USB 2.0 Material: Aramid Fiber Power: Up to 3A Jacket Type: TPE Shielding: EMI Protection with Aluminum/Mylar

Hardware		
	Warranty	Lifetime
	Connector Plating	Nickel
	Cable Jacket Material	TPE - Thermoplastic Elastomers
	Cable Shield Material	Aluminum-Mylar Foil with Braid
Performance		
	Maximum Cable Length	19.7 in [500 mm]
	Type and Rate	USB 2.0 - 480 Mbit/s
Connector(s)		
	Connector A	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)
	Connector B	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Environmental		
	Operating Temperature	0 to 80C (32 to 176F)
	Storage Temperature	0 to 80C (32 to 176F)
	Humidity	0% to 95% RH
Physical Characteristics		
	Color	Black
	Connector Style	Straight



	Wire Gauge	22/32 AWG
	Cable Length	1.6 ft [0.5 m]
	Cable OD	0.1 in [3.1 mm]
	Product Length	12.6 in [32.0 cm]
	Product Width	0.6 in [1.5 cm]
	Product Height	0.3 in [7.0 mm]
	Weight of Product	1.1 oz [30.0 g]
Packaging Information		
	Package Quantity	1
	Package Length	8.7 in [22.0 cm]
	Package Width	4.9 in [12.5 cm]
	Package Height	0.7 in [1.7 cm]
	Shipping (Package) Weight	1.2 oz [34.0 g]
What's in the Box	Included in Package	1 - USB-A to USB-C cable

^{*}Product appearance and specifications are subject to change without notice.