

20in (50cm) USB C Charging Cable, Coiled Heavy Duty Fast Charge & Sync USB-C Cable, USB 2.0 Type-C Cable, Rugged Aramid Fiber, Durable Male to Male USB Cable, Black

**Product ID:** R2CCC-50C-USB-CABLE



This 20in (50cm) coiled USB C cable can withstand the daily demands of charging and syncing your mobile devices. It contracts to 12in (32cm) making it compact and convenient to store.

The durable USB C charging cable has aramid fiber reinforcement that shelters it from the stress of frequent bends. This also lets the cable flex without over-stretching or damaging the core of the cable.

The USB C cable is constructed to prevent the connector from separating from the jacket. The extra-long strain relief molding is tested to withstand over 5,000+ bend cycles at a 180 angle.

The durable cable supports all USB 2.0 specifications providing a dependable connection for all your USB-C devices. It supports up to 3A for charging your USB C compatible devices.

R2CCC-50C-USB-CABLE is backed by a StarTech.com lifetime warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

## Features

- USB C CHARGING CABLE: Coiling cable stretches up to 20in (50cm) and contracts to 12.5in (32cm) preventing it

from being tangled; Strong but soft flexible TPE jacket, makes it easy to coil and put away in vehicle console or glove compartment

- **RUGGED DESIGN:** USB Type-C cable reinforced with aramid fiber for increased tensile strength; Tested to withstand 10000+ insertions & 5000+ bend cycles at 180 angle; Durable TPE jacket and strain relief; TPE is non-toxic, halogen free
- **FAST CHARGE AND SYNC :** Supporting up to 3A for fast charging from a USB-C port or Quick Charge power adapter, this high quality cord is designed to charge and sync your USB C devices
- **USB-C COMPATIBILITY:** Heavy duty data transfer cable allows you to charge and sync your USB Type C devices including your iPad Pro, iPad Mini, Samsung Galaxy S8, S9, S10, S20, S20+, One Plus & Google Pixel 3a, 3, 4, 5, 6 series
- **SPECS:** Length: 20in (50cm) Color: Black Connectors: USB-C to USB-C Performance: USB 2.0 Material: Aramid Fiber Power: 3A Jacket Type: TPE Shielding: EMI Protection

---

#### Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

#### Performance

Maximum Cable Length	19.7 in [500 mm]
Type and Rate	USB 2.0 - 480 Mbit/s

---

#### Connector(s)

Connector A	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)
Connector B	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)

---

#### Environmental

Operating Temperature	0 to 80C (32 to 176F)
Storage Temperature	0 to 80C (32 to 176F)
Humidity	0% to 95% RH

---

#### Physical Characteristics

Color	Black
Connector Style	Straight



Wire Gauge	22/32 AWG
Cable Length	1.6 ft [0.5 m]
Cable OD	0.1 in [3.1 mm]
Product Length	12.5 in [31.8 cm]
Product Width	0.6 in [1.5 cm]
Product Height	0.3 in [7.0 mm]
Weight of Product	1.0 oz [28.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	3.0 in [7.5 cm]
Package Width	5.7 in [14.5 cm]
Package Height	0.7 in [1.7 cm]
Shipping (Package) Weight	1.1 oz [30.0 g]

---

**What's in the Box**

Included in Package	1 - USB-C to USB-C cable
---------------------	--------------------------

---

*\*Product appearance and specifications are subject to change without notice.*

