

6in (15cm) USB C Charging Cable Right Angle - 60W PD 3A - Heavy Duty Fast Charge USB-C Cable - Black USB 2.0 Type-C - Rugged Aramid Fiber - Short USB Charging Cord

Product ID: R2CCR-15C-USB-CABLE



This rugged 6in (15cm) USB-C right angle cable can be used to connect and/or charge a USB peripheral. Conveniently connect USB-C enabled devices at a right angle to the cable for organized cable routing solutions.

The durable USB charging cable features aramid fiber reinforcement that protects the cable from the stress of frequent bends. This allows the cable to flex without over-stretching or damaging the core components of the cable.

The USB cable has been designed to prevent cable/connector strain. The extra-long strain relief moldings have been tested to withstand over 5,000+ bend cycles at a 180 angle.

The durable cable supports all USB specifications up to USB 2.0, providing a dependable connection for USB-C peripheral devices. It supports up to 3A for charging USB-C-enabled devices.

This product is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility





Applications

Features

• RIGHT ANGLE USB-C CABLE: Short 6in (15cm) USB C charging cable features a right angle USB-C connector -



Ideal for tight spots allowing the cable to run flush with the device - Reduces strain on the port and connector vs. a straight angled cable

- RUGGED DESIGN: USB Type-C cable reinforced with aramid fiber for increased tensile strength Tested to withstand 10000+ insertions and 5000+ bend cycles at 180 angle Durable TPE jacket and strain reliefs resist damage from repeated use
- FAST CHARGE AND SYNC: Supports Power Delivery up to 60W at 3A for fast charging from a USB port or Quick Charge enabled port/power adapter High quality cord designed to charge and sync USB-C devices Use with USB-C ports and 18W/30W/45W/60W chargers
- USB-C COMPATIBILITY: Heavy duty data transfer cable to charge and sync USB Type-C devices including iPad Pro/iPad/Mini, Samsung Galaxy S20/S20+/S21/S21+/S22/S22+, One Plus, and Google Pixel 6/Pro/6a Charge from USB-C docks/portable chargers/car chargers
- SPECS: Length: 6in (15cm) Color: Black Connectors: Male USB-C to Male USB-C Performance: USB 2.0 Braid Material: Aramid Fiber Power: Up to 60W/3A Jacket Type: TPE Shielding: EMI Protection with Aluminum/Mylar Backed for Life

Warranty	Lifetime
Connector Plating	Gold and Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid
Maximum Cable Length	0.5 ft [0.2 m]
Type and Rate	USB 2.0 - 480 Mbit/s
Connector A	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)
Connector B	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)
Power Delivery	60W
Operating Temperature	0 to 50C (32 to 122F)
Storage Temperature	0 to 50C (32 to 122F)
Humidity	0%~85%
	Connector Plating Cable Jacket Material Cable Shield Material Maximum Cable Length Type and Rate Connector A Connector B Power Delivery Operating Temperature Storage Temperature



Physical Characteristics

Color Black

Connector Style Right Angle to Straight

Wire Gauge 22/32 AWG

Cable Length 0.5 ft [0.2 m]

Cable OD 0.1 in [3.1 mm]

Product Length 6.0 in [15.2 cm]

Product Width 1.1 in [2.9 cm]

Product Height 0.5 in [1.2 cm]

Weight of Product 0.3 oz [9.0 g]

Packaging Information

Package Quantity 1

Package Length 8.7 in [22.0 cm]

Package Width 5.0 in [12.8 cm]

Package Height 1.2 in [3.0 cm]

Shipping (Package)

Weight

0.5 oz [14.0 g]

What's in the Box

Included in Package 1 - USB-C to Angled USB-C Cable

^{*}Product appearance and specifications are subject to change without notice.