
## Cable Glands Waterproof, Dustproof and Breathable Multicomp



Serial No	Name	Material	Qty.
1	Sealing Nut	PA	
2	Seal	EPDM	
3	Body	PA	1
4	Gasket	EPDM	
5	Lock Nut	PA	

RoHS

Compliant

Name	Parameter	Unit
Air volume	200 to 300	ml/min@70mbar
Recommended Opening Size (Through Hole)	Ø25.2	mm
Cable Range	13 to 18	mm
*Torque for Sealing Nut	5 to 6	N.m
*Torque for Body	3.5 to 5	N.m
Operating Temp.	-40 to 100	°C
Protection Degree	IP67	-

Dimensions : Millimetres

## Note

1. "" indicates that parameters may change during installation.

2. The installation torque value can be adjusted according to the actual situation of customers.

## **Part Number Table**

Description	Part Number
Cable Gland Kit with Strain Relief, Metric, 13mm to 18mm, IP67	MP010344

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet sh

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

