



# **SUMMARY**

#### # Wires



Image is for illustrative purpose only

Series 1K

Termination type No contacts / Accessory

IP rating 68

AWG wire size 0.00 - 0.00

Cable Ø 0.00 - 0.00 mm

**Status** active

### **Download**

Request a quote

Catalog

## **TECHNICAL DETAILS**

#### **Mechanics**

Shell Style/Model BRE\*: Cap for receptacle

**Keying** No keying

Housing Material Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces

**Weight** 17.32 g

### **Performance**

Configuration

Insulator

**Rated Current** 

### **Others**

Endurance (Shell): 5000 mating cycles Temp (min / max): -50°C / +135°C


Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [ 6 ms]

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Climatical Category: 50/175/21 Shielding (min): 95 dB (10 MHz) Shielding (min): 80 dB (1 GHz) Salt Spray Corrosion: >144 hr

# **DRAWINGS**



No keying

## **Dimensions**

	A	В	L	М	N
mm.	17	12	20	6	85
in.	0,67	0,47	0,79	0,24	3,35

# **RECOMMENDED BY LEMO**

#### **Tools**

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.