



www.lemo.com

## **SUMMARY**

#### # Wires

Low voltage 7



Image is for illustrative purpose only

Series 0B

**Termination type** Female solder

IP rating 50

AWG wire size 34.00 - 28.00

Cable Ø 0.00 - 0.00 mm

**Status** active

Matching parts FGG.0B.307.CLAD52Z

#### **Download**

Request a quote

Catalog

## **TECHNICAL DETAILS**

#### **Mechanics**

Shell Style/Model EC\*: Fixed receptacle with two nuts (back panel mounting)

Keying 1 key (alpha=0, plug: male contacts, receptacle: female contacts)

Housing Material

Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290]

brass latch sleeve and mid pieces

Weight 5.02 g

#### **Performance**

Configuration 0B.307 : 7 Low Voltage Insulator L: PEEK (UL 94 / V-0/1.5)

Rated Current 2.5 Amps

### **Specifications**

Contact Type: Solder

Contact Dia.: 0.5 mm (0.02in) Bucket Dia.: 0.45 mm (0.018in)

Max. Solid Conductor: 0.09 mm<sup>2</sup> (AWG 28) Max. Stranded Conductor: 0.09 mm<sup>2</sup> (AWG 28)

R (max): 8.7 mOhm

Vtest (contact-shell): 700 V (AC), 990 V (DC) Vtest (contact-contact): 800 V (AC), 1130 V (DC)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

#### **Others**


Endurance (Shell): 5000


Temp (min / max): -55°C / +250°C

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [ 6 ms] Climatical Category: 50/175/21 Shielding (min): 75 dB (10 MHz) Shielding (min): 40 dB (1 GHz) Salt Spray Corrosion: >1000 hr

# **DRAWINGS**







#### **Dimensions**

|     | А    | В    | Е    | L    | М    | N    | <b>S</b> 1 | <b>S</b> 3 | e      |
|-----|------|------|------|------|------|------|------------|------------|--------|
| mm. | 12   | 12.4 | 5.5  | 20.7 | 2.5  | 19.1 | 8.2        | 11         | M9x0.6 |
| in. | 0,47 | 0,49 | 0,22 | 0,81 | 0,10 | 0,75 | 0,32       | 0,43       |        |

# **RECOMMENDED BY LEMO**

## Tools

Spanner 2: DCH.91.121.PA

Spanner wrench: Socket for torque wrench DCM.65.100.AZ and DCM.0S.M09.4

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

### **Cables**

| CMN.07.T28.044PGZE |     | Grey  |                  |
|--------------------|-----|-------|------------------|
| CMN.07.T28.044PNZE |     |       |                  |
| 7041               | PVC | Grey  |                  |
| 7050               | PVC | Black | <b>&gt;:====</b> |
| 717920             | PVC | Grey  | >€               |
| CTR.75.030.121875G | PVC | Grey  | <b>&gt;</b> □ □€ |

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.