

# ECG.1B.306.CLL

## SUMMARY

#### # Wires

Low voltage

6



Image is for illustrative purpose only

Series	1B		
Termination type	Female solder		
IP rating	50		
AWG wire size	30.00 - 22.00		
Cable Ø	0.00 - 0.00 mm		
Status	active		
Matching parts	FGG.1B.306.CLAD42Z		

Download Request a quote Catalog

# **TECHNICAL DETAILS**

### **Mechanics**

Shell Style/Model	EC*: Fixed receptacle with two nuts (back panel mounting)
Keying	1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Housing Material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Weight	10.32 g
Performance	
Configuration	1B.306 : 6 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated Current	7 Amps
Specifications	


Contact Type: Solder Contact Dia.: 0.7 mm (0.028in) Bucket Dia.: 0.8 mm (0.031in) Max. Solid Conductor: 0.34 mm^2 (AWG 22) Max. Stranded Conductor: 0.34 mm^2 (AWG 22) R (max): 6.1 mOhm Vtest (contact-shell): 1200 V (AC), 1700 V (DC) Vtest (contact-contact): 1050 V (AC), 1490 V (DC)


LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

### Others

Endurance (Shell): 5000 Temp (min / max): -55°C / +250°C Humidity (max): <=95% [at 60 deg C /140 F] Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [ 6 ms] Climatical Category: 50/175/21 Shielding (min): 75 dB (10 MHz) Shielding (min): 40 dB (1 GHz) Salt Spray Corrosion: >1000 hr

### DRAWINGS







### Dimensions

	А	В	E	L	Μ	N	S1	S3	e
mm.	16	15.8	6	23	3.5	21.1	10.5	14	M12x1.0
in.	0,63	0,62	0,24	0,91	0,14	0,83	0,41	0,55	

### **RECOMMENDED BY LEMO**

### Tools

Spanner 2:

Spanner wrench:

DCH.91.161.PA

#### Socket for torque wrench DCM.1S.M12.4

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

### Cables

CMN.06.T26.037QGZE	TPR (medical)	Grey	▶
CMN.06.T28.031PGCE	PVC	GREY	
CMN.06.T28.031PGZE		Grey	▶
CMN.06.T28.031PNCE	PVC	Black	
CMN.06.T28.031PNZE			▶€
CMN.06.T28.042QBCE	TPR (medical)		
CMN.06.T28.044PGZE		Grey	▶
CMN.06.T28.044PNZE			▶€
106220	PVC	Black	
106240	PTFE	White	▶====€
12080	PVC	Grey	
160140	PVC	Grey	
160240	PVC	Black	
160260	PVC	Black	
260250	PVC	Grey	>
60260	PTFE	White	▶====€
6280	PVC	Black	

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.