

www.lemo.com

# EEG.1B.307.CLL

## **SUMMARY**

### # Wires

Low voltage 7



Image is for illustrative purpose only

Series 1B

Termination type Female solder

IP rating 50

AWG wire size 30.00 - 22.00

Cable Ø 0.00 - 0.00 mm

Status active

Matching parts FGG.1B.307.CLAD52Z

## **Download**

Request a quote

Catalog

## **TECHNICAL DETAILS**

#### **Mechanics**

Shell Style/Model EE\*: Fixed receptacle, nut fixing (back panel mounting)

Keying 1 key (alpha=0, plug: male contacts, receptacle: female contacts)

Housing Material

Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290]

brass latch sleeve and mid pieces

Weight 10.44 g

### **Performance**

Configuration 1B.307 : 7 Low Voltage Insulator L: PEEK (UL 94 / V-0/1.5)

Rated Current 7 Amps

## **Specifications**

Contact Type: Solder

Contact Dia.: 0.7 mm (0.028in) Bucket Dia.: 0.8 mm (0.031in)

Max. Solid Conductor: 0.34 mm<sup>2</sup> (AWG 22) Max. Stranded Conductor: 0.34 mm<sup>2</sup> (AWG 22)

R (max): 6.1 mOhm

Vtest (contact-shell): 1050 V (AC), 1490 V (DC) Vtest (contact-contact): 950 V (AC), 1340 V (DC)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## **Others**


Endurance (Shell): 5000


Temp (min / max): -55°C / +250°C

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [ 6 ms] Climatical Category: 50/175/21 Shielding (min): 75 dB (10 MHz) Shielding (min): 40 dB (1 GHz) Salt Spray Corrosion: >1000 hr

## **DRAWINGS**







## **Dimensions**

	А	В	E	L	М	N	Р	S1	S2	e
mm.	16	16	6.5	23	3.5	21.1	11	10.5	13	M12x1.0
in.	0,63	0,63	0,26	0,91	0,14	0,83	0,43	0,41	0,51	

## **RECOMMENDED BY LEMO**

## **Tools**

Spanner wrench: Socket for torque wrench DCM.65.130.AZ and DCM.1S.M12.4

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Cables

CMN.07.T26.037QGZE	TPR (medical)	Grey	
CMN.07.T28.044PGZE		Grey	
CMN.07.T28.044PNZE			
270250	PVC	Grey	
70140	PVC	Grey	
7041	PVC	Grey	•
7050	PVC	Black	
717920	PVC	Grey	>□ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □
CTR.75.030.121875G	PVC	Grey	>□ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.