

ERA.0S.302.CLL

SUMMARY

Wires

Low voltage

2

|--|

Image is for illustrative purpose only

Series	OS
Termination type	Female solder
IP rating	50
AWG wire size	30.00 - 22.00
Cable Ø	0.00 - 0.00 mm
Status	active
Matching parts	FFA.0S.302.CLAC22

Download

Request a quote Catalog

TECHNICAL DETAILS

Mechanics

Shell Style/M	\odel	ERA*: Fixed receptacle, nut fixing
Keying		Hermaphroditic keying (half moon insert) with female pin 1
Housing Mate	erial	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Weight		4.11 g
Performance	1	
Configuratio	n	OS.302 : 2 Low Voltage
Insulator		L: PEEK (UL 94 / V-0/1.5)
Rated Currer	nt	10 Amps

Specifications


Contact Type: Solder Contact Dia.: 0.9 mm (0.0354in) Bucket Dia.: 0.8 mm (0.031in) Max. Solid Conductor: 0.34 mm² (AWG 22) R (max): 4.8 mOhm Vtest: 1500 V (AC), 2100 V (DC)


Others

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Endurance (Shell): 5000 mating cycles Temp (min / max): -55°C / +250°C Humidity (max): <=95% [at 60 deg C /140 F] Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [6 ms] Climatical Category: 50/175/21 Shielding (min): 75 dB (10 MHz) Shielding (min): 40 dB (1 GHz) Salt Spray Corrosion: >1000 hr

DRAWINGS







Dimensions

	А	В	E	L	м	S1	\$3	e
mm.	10	12.5	7	18.5	1.2	8.2	11	M9x0.6
in.	0,39	0,49	0,28	0,73	0,05	0,32	0,43	

RECOMMENDED BY LEMO

Tools

Spanner wrench:

Socket for torque wrench DCM.0S.M09.4

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

CMN.02.T28.030PGCE	PVC	GREY	~ ~
CMN.02.T28.030PGZE		Grey	
CMN.02.T28.030PNCE	PVC	Black	-
CMN.02.T28.030PNZE			
102080	PVC	Grey	
120184	PVC	Black	
120240	PVC	Black	
120250	PVC	Grey	-
20140	PVC	Grey	
20140	PVC	Grey	
20141	PVC	Grey	
20142	PVC	Red	
20143	PVC	Green	
20144	PVC	Black	
20145	PVC	Yellow	
20146	PVC	Black	
20240	PTFE	White	«»
20260	PVC	Black	
20264	PVC	Black	-
20266	PVC	Violet	-
2050	PVC	Black	-
20550	PUR	Black	
20560	PUR	White	
2080	PVC	Grey	
2221	PVC	Black	700
2260	PTFE	White	«»
2280	PVC	Black	
4082	PVC	Grey	
CMB.02.210.635	PUR	Black	

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.