

FFA.0S.303.CLAC32

SUMMARY

Wires

Low voltage 3



Image is for illustrative purpose only

Series 0S

Termination type Male solder

IP rating 50

AWG wire size 32.00 - 24.00

Cable Ø 2.30 - 3.20 mm

Status active

Matching parts ERA.0S.303.CLL

Download

Request a quote

Eplan Catalog

TECHNICAL DETAILS

Mechanics

Shell Style/Model FFA*: Straight plug, cable collet

Keying Hermaphroditic keying (half moon insert) with male pin 1

Housing Material

Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290]

brass latch sleeve and mid pieces

Weight 7.79 g

Performance

Configuration 0S.303 : 3 Low Voltage Insulator L: PEEK (UL 94 / V-0/1.5)

Rated Current 7 Amps

Specifications

Contact Type: Solder

Contact Dia.: 0.7 mm (0.028in) Bucket Dia.: 0.6 mm (0.024in)

Max. Solid Conductor: 0.25 mm² (AWG 24) Max. Stranded Conductor: 0.14 mm² (AWG 26)

R (max): 6.1 mOhm

Vtest: 1060 V (AC), 1500 V (DC)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Others

Endurance (Shell): 5000 mating cycles Temp (min / max): -55°C / +250°C

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [6 ms] Climatical Category: 50/175/21 Shielding (min): 75 dB (10 MHz) Shielding (min): 40 dB (1 GHz) Salt Spray Corrosion: >144 hr

DRAWINGS





Dimensions

	А	L	М	S2
mm.	9	34.5	24.5	6.5
in.	0,35	1,36	0,96	0,26

RECOMMENDED BY LEMO

Tools

Spanner wrench: DCD.0S.ZZZ.PA065

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cables

CMN.03.T28.031PGCE	PVC	GREY	
CMN.03.T28.031PGZE		Grey	-
CMN.03.T28.031PNCE	PVC	Black	>=======
CMN.03.T28.031PNZE			-
30141	PVC	Grey	
3041	PVC	Grey	>€
3050	PVC	Black	> = = = = = = = = = = = = = = = = = = =
3081	PVC	Black	

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.