

www.lemo.com

# FGG.1B.305.CLAD72Z

# **SUMMARY**

#### # Wires

Low voltage 5



Image is for illustrative purpose only

Series 1B

Termination type Male solder

IP rating 50

AWG wire size 30.00 - 22.00

Cable Ø 6.30 - 7.20 mm

Status active

Matching parts EGG.1B.305.CLL

PHG.1B.305.CLLD72Z

#### **Download**

Request a quote

Eplan Catalog

See video assembly instructions

## **TECHNICAL DETAILS**

#### Mechanics

Shell Style/Model FG\*: Straight plug, cable collet and nut for fitting a bend relief

**Keying** 1 key (alpha=0, plug: male contacts, receptacle: female contacts)

Housing Material

Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290]

brass latch sleeve and mid pieces

Variant Z: Nut for fitting a bend relief

**Weight** 15.32 g

#### **Performance**

Configuration 1B.305 : 5 Low Voltage Insulator L: PEEK (UL 94 / V-0/1.5)

Rated Current 9 Amps

## **Specifications**

Contact Type: Solder

Contact Dia.: 0.9 mm (0.035in) Bucket Dia.: 0.8 mm (0.031in)

Max. Solid Conductor: 0.34 mm^2 (AWG 22) Max. Stranded Conductor: 0.34 mm^2 (AWG 22)

R (max): 4.8 mOhm

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Vtest (contact-shell): 1150 V (AC), 1630 V (DC) Vtest (contact-contact): 1250 V (AC), 1770 V (DC)

### **Others**


Endurance (Shell): 5000

Temp (min / max): -55°C / +250°C

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [ 6 ms] Climatical Category: 50/175/21 Shielding (min): 75 dB (10 MHz) Shielding (min): 40 dB (1 GHz) Salt Spray Corrosion: >1000 hr

# **DRAWINGS**



### **Dimensions**

	А	L	М	S1	S2
mm.	12	42	31	10	9
in.	0,47	1,65	1,22	0,39	0,35

# **RECOMMENDED BY LEMO**

### **Tools**

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Spanner wrench: DCD.1B.ZZZ.PA090
Caps: BFG.1B.100.PCSG

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.