



www.lemo.com

SUMMARY

Wires



Image is for illustrative purpose only

Series 0E

Termination type No contacts / Accessory

IP rating (

AWG wire size 0.00 - 0.00

Cable Ø 0.00 - 0.00 mm

Status active

Download

Request a quote

Catalog

TECHNICAL DETAILS

Mechanics

Shell Style/Model GCA*: Earthing washer

Keying No keying

Housing Material Brass (CuSnZn plated)

Weight .43 g

Performance

Configuration

Insulator

Rated Current

Others

Temp (min / max): -55° C / $+200^{\circ}$ C


Humidity (max): $\leq 95\%$ [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [6 ms] Climatical Category: 50/175/21

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Shielding (min): 95 dB (10 MHz) Shielding (min): 80 dB (1 GHz)

DRAWINGS



Dimensions

	А	В	L	N
mm.	17	14.1	0.5	27.5
in.	0,67	0,56	0,02	1,08

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.