



SUMMARY

Wires



Image is for illustrative purpose only

Series 0B

Termination type No contacts / Accessory

IP rating (

AWG wire size 0.00 - 0.00

Cable Ø 3.00 - 3.40 mm

Status active

Download

Request a quote

Catalog

TECHNICAL DETAILS

Mechanics

Shell Style/Model GMA*: Bend relief Black

Keying No keying

Housing Material Brass (gold plated [ISO 27874]) shell, collet nut, brass latch sleeve and mid pieces

Variant N: Black

Weight .43 g

Performance

Configuration

Insulator


Rated Current

Others

Temp (min / max): -40° C / $+80^{\circ}$ C

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

DRAWINGS



No keying

Dimensions

	Α	L
mm.	3.0	24
in.	0,12	0,94

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.