

# GRA.00.269.GN

### **SUMMARY**

#### # Wires



Image is for illustrative purpose only

Series	00		
Termination type	No contacts / Accessory		
IP rating	0		
AWG wire size	0.00 - 0.00		
Cable Ø	0.00 - 0.00 mm		
Status	active		

Download

Request a quote Catalog

# **TECHNICAL DETAILS**


#### **Mechanics**

Shell Style/Model	GRA*: Insulating washer
Keying	No keying
Housing Material	PEEK (Polyetheretherketone) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Weight	.06 g
Performance Configuration Insulator Rated Current	

#### Others

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## DRAWINGS



### No keying

#### Dimensions

	А	В	L	м	S	т
mm.	10	8.8	1.8	1	6.4	8
in.	0,39	0,35	0,07	0,04	0,25	0,31

### **RECOMMENDED BY LEMO**

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.