

# PRG.MO.4GL.LC52J

## **SUMMARY**

#### # Wires

Low voltage 4



Image is for illustrative purpose only

Series 1P

**Termination type** Female solder

IP rating 50

AWG wire size 0.00 - 22.00

Cable Ø 4.00 - 5.20 mm

Status active

Matching parts PAG.M0.4GL.AC52J

#### **Download**

Request a quote

Catalog

## **TECHNICAL DETAILS**

#### Mechanics

Shell Style/Model PR\*: Free receptacle with cable collet

Keying 1 key (alpha=0; Plug: male contact; Receptacle: female contact)

Housing Material PSU (Polysulfone), gray

Variant J: Yellow collet nut

Weight 4.54 g

#### **Performance**

Configuration 1P.M04: 4 Low Voltage Insulator L: PEEK (UL 94 / V-0/1.5)

Rated Current 8 Amps

### **Specifications**

Contact Type: Solder

Contact Dia.: 0.9 mm (0.0354in) Bucket Dia.: 0.8 mm (0.031in)

Max. Solid Conductor: 0.34 mm^2 (AWG 22) Max. Stranded Conductor: 0.34 mm^2 (AWG 22)

R (max): 4.5 mOhm

Test voltage (kV rms) Contact-contact: 1.2

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Air clearance min.: 1.2 mm Creepage distance min.: 1.2 mm


### **Others**


Endurance (Shell): >2000 mating cycles Temp (min / max): -50°C / +150°C

F ret (min): 50 N F ret (max): 150 N

Steam sterilization: > 100 times (with potting on rear connection)

## **DRAWINGS**







### **Dimensions**

	A	L
mm.	14	40
in.	0,55	1,57

# **RECOMMENDED BY LEMO**

#### **Tools**

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## **Cables**

CMN.04.T22.047QGC	TPR	Grey	
CMN.04.T22.048QGZE	TPR (medical)	Grey	-
140240	PVC	Black	-
140250	PVC	Grey	
40140	PVC	Black	
40260	PVC	Black	-
4080	PVC	Grey	
4221	PVC	Black	
4280	PVC	Black	-
80080	PVC	Grey	
80082	PVC	Red	
80084	PVC	Black	

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.