



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/19/2021	GUITADAURO



ITEM NUMBER	LENGTH INCHES [MM]
N515P-N515R3-15-03F	36.0 ± 0.4 [910 ± 10.0]
N515P-N515R3-15-06F	72.0 ± 0.8 [1830 ± 20.0]
N515P-N515R3-15-10F	120.0 ± 1.2 [3050 ± 30.0]

NOTES:

- VOLTAGE RATING:
DIELECTRIC VOLTAGE WITHSTAND TEST: 1500V / 1 Sec
CONDUCTOR RESISTANCE ≤ 8.88Ω/1000M
VOLTAGE RATING AC 300V
- CABLE MARKING :
(UL) E135710-F5 SJT 3X14AWG 105°C 300V VW-1
CSA LL95737 SJT3X2.08mm2(14AWG) FT2 YFC-BONEAGLE
- OPTIONAL LABELS:
OPTIONAL LABEL(S) MAY INCLUDE
UL, CURRENT AND/OR WARNING
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH SPEC. PS-0031.
- ALL DIMENSIONS FOR REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [1.3]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY MVEERAPPAN	19-10-2021	
THIRD-ANGLE PROJECTION 	CHECKED BY DFRISIELLO	10/19/2021	CATEGORY POWER PRODUCTS
	APPROVED BY GUITADAURO	10/19/2021	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION N5-15P - 3N5-15R Power Cord, 15A, 125V		SIZE A CAGE CODE 43321 ITEM NO. N515P-N515R3-15 REV. A
COLOR VARIATIONS MAY OCCUR	SCALE: NONE	CAD FILE: N515P-N515R3-15.SLDDRW	SHEET 1 OF 1