

Datasheet

PFA Insulated Flat Pair Thermocouple Cable



- Single pair of PFA insulated conductors, laid flat with PFA jacket
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids
- Tolerance Class 1 for optimum accuracy
- Insulation rating -75°C to 260°C
- Colour code (cores & jacket) to IEC-584-3

Type	Conductors	Reel Length	Manufacturers Code	Order Code
E	7/0.2mm	10m	WE-250-D	XF-1593-FAR
E	7/0.2mm	25m	WE-250-D	XF-1594-FAR
E	7/0.2mm	50m	WE-250-D	XF-1595-FAR
E	7/0.2mm	100m	WE-250-D	XF-1596-FAR
J	7/0.2mm	10m	WJ-248-D	XF-1305-FAR
J	7/0.2mm	25m	WJ-248-D	XF-571-FAR
J	7/0.2mm	50m	WJ-248-D	XF-572-FAR
J	7/0.2mm	100m	WJ-248-D	XF-1294-FAR
K	1/0.2mm	25m	WK-609-D	XF-1677-FAR
K	1/0.2mm	100m	WK-609-D	XF-1678-FAR
K	1/0.3mm	10m	WK-356-D	XF-1291-FAR
K	1/0.3mm	25m	WK-356-D	XF-573-FAR
K	1/0.3mm	50m	WK-356-D	XF-1310-FAR
K	1/0.3mm	100m	WK-356-D	XF-1276-FAR
K	1/0.508mm	25m	WK-306-D	XF-1260-FAR
K	1/0.508mm	50m	WK-306-D	XF-1252-FAR
K	1/0.508mm	100m	WK-306-D	XF-1779-FAR
K	7/0.2mm	10m	XS-751-D	XF-1309-FAR
K	7/0.2mm	25m	XS-751-D	XF-574-FAR
K	7/0.2mm	50m	XS-751-D	XF-575-FAR
K	7/0.2mm	100m	XS-751-D	XF-576-FAR
N	7/0.2mm	25m	WN-121-D	XF-581-FAR
T	1/0.3mm	25m	WT-203-D	XF-577-FAR
T	1/0.3mm	50m	WT-203-D	XF-1761-FAR
T	1/0.5mm	10m	WT-309-D	XF-1707-FAR
T	1/0.5mm	25m	WT-309-D	XF-1705-FAR
T	1/0.5mm	50m	WT-309-D	XF-1706-FAR
T	1/0.5mm	100m	WT-309-D	XF-1708-FAR
T	7/0.2mm	25m	WT-305-D	XF-578-FAR
T	7/0.2mm	50m	WT-305-D	XF-579-FAR
T	7/0.2mm	100m	WT-305-D	XF-580-FAR