

## Datasheet

### IEC Thermocouple Cable – PFA Insulated Twin Twisted Pair



- PFA Teflon® twin twisted pair for extending or making simple thermocouples
- Single pair of PFA insulated conductors twisted together
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids, gasses, steam & pressure
- Tolerance Class 1 for optimum accuracy
- Insulation rating -75°C to 260°C
- Colour coded to IEC-584

Type	Conductors	Reel Length	Manufacturers Code	Order Code
J	1/0.2mm	10m	WJ-251-D	<a href="#">XF-1627-FAR</a>
J	1/0.2mm	25m	WJ-251-D	<a href="#">XF-1625-FAR</a>
J	1/0.2mm	50m	WJ-251-D	<a href="#">XF-1626-FAR</a>
J	1/0.2mm	100m	WJ-251-D	<a href="#">XF-1628-FAR</a>
J	1/0.3mm	10m	WJ-252-D	<a href="#">XF-1631-FAR</a>
J	1/0.3mm	25m	WJ-252-D	<a href="#">XF-1629-FAR</a>
J	1/0.3mm	50m	WJ-252-D	<a href="#">XF-1630-FAR</a>
J	1/0.3mm	100m	WJ-252-D	<a href="#">XF-1632-FAR</a>
J	1/0.508mm	10m	WJ-253-D	<a href="#">XF-1635-FAR</a>
J	1/0.508mm	25m	WJ-253-D	<a href="#">XF-1634-FAR</a>
J	1/0.508mm	50m	WJ-253-D	<a href="#">XF-1633-FAR</a>
J	1/0.508mm	100m	WJ-253-D	<a href="#">XF-1636-FAR</a>
<b>IEC-584</b>				
K	1/0.2mm	50m	WK-203-D	<a href="#">XF-567-FAR</a>
K	1/0.2mm	100m	WK-203-D	<a href="#">XF-568-FAR</a>
K	1/0.315mm	10m	WK-204-D	<a href="#">XF-1794-FAR</a>
K	1/0.315mm	25m	WK-204-D	<a href="#">XF-1790-FAR</a>
K	1/0.315mm	50m	WK-204-D	<a href="#">XF-569-FAR</a>
K	1/0.315mm	100m	WK-204-D	<a href="#">XF-1764-FAR</a>
K	1/0.508mm	25m	WK-206-D	<a href="#">XF-1781-FAR</a>
K	1/0.508mm	50m	WK-206-D	<a href="#">XF-1765-FAR</a>
K	1/0.508mm	100m	WK-206-D	<a href="#">XF-1810-FAR</a>
K	7/0.2mm	50m	XS-752-D	<a href="#">XF-570-FAR</a>

N	1/0.2mm	10m	WN-131-D	XF-1683-FAR
N	1/0.2mm	25m	WN-131-D	XF-1684-FAR
N	1/0.2mm	50m	WN-131-D	XF-1685-FAR
N	1/0.2mm	100m	WN-131-D	XF-1686-FAR
T	1/0.508mm	10m	WT-302-D	XF-1699-FAR
T	1/0.508mm	25m	WT-302-D	XF-1697-FAR
T	1/0.508mm	50m	WT-302-D	XF-1698-FAR
T	1/0.508mm	100m	WT-302-D	XF-1700-FAR
T	1/0.2mm	50m	WT-304-D	XF-563-FAR
T	1/0.2mm	100m	WT-304-D	XF-564-FAR
T	1/0.315mm	25m	WT-306-D	XF-1795-FAR
T	1/0.315mm	50m	WT-306-D	XF-565-FAR
T	7/0.2mm	25m	WT-307-D	XF-1797-FAR
T	7/0.2mm	50m	WT-307-D	XF-566-FAR