

Datasheet

Type 'K' Exposed Junction Thermocouple with Miniature Plug



- Fast response, welded exposed junction
- PFA Teflon® insulated flat pair
- Single pair of PFA insulated conductors, laid flat with PFA jacket
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids
- Thermocouple type K
- 1/0.3mm or 1/0.5mm
- 1, 2, 3, 5 OR 10 metre lengths available
- Terminated with a miniature flat pin plug
- Tolerance Class 1 for optimum accuracy
- Insulation rating -75°C to 260°C
- Colour code (cores & jacket) to IEC-584-3

T/C Type	Conductors	Cores	Jacket	Length	Order Code
K	1/0.3mm	+Green/-White	Green	1m	<a href="#">XF-1568-FAR</a>
K	1/0.3mm	+Green/-White	Green	2m	<a href="#">XF-1569-FAR</a>
K	1/0.3mm	+Green/-White	Green	3m	<a href="#">XF-1570-FAR</a>
K	1/0.3mm	+Green/-White	Green	5m	<a href="#">XF-1571-FAR</a>
K	1/0.5mm	+Green/-White	Green	1m	<a href="#">XF-1572-FAR</a>
K	1/0.5mm	+Green/-White	Green	2m	<a href="#">XF-1573-FAR</a>
K	1/0.5mm	+Green/-White	Green	3m	<a href="#">XF-1574-FAR</a>
K	1/0.5mm	+Green/-White	Green	5m	<a href="#">XF-1575-FAR</a>
K	1/0.5mm	+Green/-White	Green	10m	<a href="#">XF-1831-FAR</a>