

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300621066](#)  
**Status:** **Active**  
**Overview:** BradPower Cordsets and Receptacles  
**Description:** BradPower A-Size (7/8"-M22) Double-Ended Cordset, 4 Poles, Male (Straight) to Female (Straight), 14 AWG, Black TPE Cable, 10.0m (32.81') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E258922

**General**

|                    |                                                    |
|--------------------|----------------------------------------------------|
| Product Family     | Industrial Cordsets                                |
| Series             | <a href="#">130062</a>                             |
| Connector End A    | BradPower A-Size (7/8"-M22)                        |
| Connector End B    | BradPower A-Size (7/8"-M22)                        |
| IP Rating          | IP67                                               |
| Material - Contact | Copper Alloy                                       |
| Overview           | <a href="#">BradPower Cordsets and Receptacles</a> |
| Product Name       | BradPower A-Size                                   |
| Protocol           | FF                                                 |
| Region             | Europe                                             |
| Taxonomy           | Circular Industrial Cordsets                       |
| Type               | Double Ended                                       |
| UPC                | 78172556374                                        |

**Physical**

|                               |                         |
|-------------------------------|-------------------------|
| Cable Diameter                | 9.47mm (.373")          |
| Cable Length                  | 10.0m (32.81')          |
| Color - Cable Jacket          | Black                   |
| Coupling Style                | Threaded                |
| Gender                        | Female-Male             |
| Keyway                        | Single                  |
| LED Indicator                 | No                      |
| Material - Cable Jacket       | TPE                     |
| Material - Connector Body     | TPE                     |
| Material - Coupling Nut       | Black Epoxy Coated Zinc |
| Material - Plating Mating     | Gold                    |
| Net Weight                    | 1054.000/g              |
| Orientation                   | Straight to Straight    |
| Poles                         | 4                       |
| Temperature Range - Operating | -20° to +90°C           |
| Wire Size AWG                 | 14                      |
| Wire/Cable Type               | TC-ER                   |

**Electrical**

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 15.0A |
| Voltage - Maximum             | 600V  |

**Material Info**

Engineering Number 114030K21M100G

**Reference - Drawing Numbers**

Sales Drawing SD-130062-023-001



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per -  
D(2022)4187-DC (10  
June 2022)

Lead

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Reviewed

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[130062 Series](#)

This document was generated on 10/31/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**