

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200680176](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change (M12) In-Line Splitter, 4 Pole, 1 x 4-Pole Male (Straight) to 2 x 3-Pole Female (Straight), 18 AWG TPE Cable, 2.0m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E152210

General

Product Family Industrial Tees and Splitters
 Series [120068](#)
 IP Rating IP67
 Overview [Brad Micro-Change \(M12\) Connectors](#)
 Product Name Micro-Change (M12)
 Taxonomy Industrial Tees and Splitters
 Type Splitter - In-line
 UPC 78678851082

Physical

Color - Cable Jacket Yellow
 Drop Connector N/A
 Drop Gender N/A
 Keyway Single
 LED Indicator No
 Left Trunk Connector Micro-Change (M12)
 Left Trunk Gender Male
 Leg 1 Length 0.60m
 Leg 2 Length 0.60m
 Material - Cable Jacket PVC
 Material - Connector Body PUR
 Material - Coupling Nut Nickel-plated Brass
 Net Weight 24.000/g
 Poles 3 Female/4 Male
 Right Trunk Connector Micro-Change (M12)
 Right Trunk Gender Female
 Temperature Range - Operating -30°C TO +80°C

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum 250V AC/DC

Material Info

Engineering Number 884A30A09M006

Reference - Drawing Numbers

Sales Drawing SD-120068-024-001



Series image - Reference only

EU ELV

Compliant with Exemption 3

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Compliant with

Exemption 3

Not Contained

Search Parts in this Series

[120068 Series](#)