

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1201080008](#)
Status: **Active**
Overview: Brad Industrial Ethernet Solutions
Description: Double-Ended RJ-45 Cordset, 4 Poles, Male (Straight) to Male (Straight), 24 AWG, Teal Unshielded PVC Cable, 1.0m (3.28') Length, 6.35mm (.250") Diameter

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E361772

General

Product Family	Industrial Cordsets
Series	120108
Connector End A	RJ-45 (standard)
Connector End B	RJ-45 (standard)
IP Rating	IP20
Material - Contact	Phosphor Bronze
Overview	Brad Industrial Ethernet Solutions
Performance Category	5e
Product Name	Industrial Ethernet
Region	America, Asia, Europe
Taxonomy	Circular Industrial Cordsets
Type	Double Ended
UPC	78678889847

Physical

Cable Diameter	6.35mm (.250")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Teal
Coupling Style	Push and Latch
Gender	Male-Male
Keyway	N/A
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	Polycarbonate
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Net Weight	49.578/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20° to +75°C
Wire Size AWG	24
Wire/Cable Type	Unshielded PVC

Electrical


Current - Maximum per Contact	0.5A
Voltage - Maximum	30V AC / 60V DC

Material Info

Engineering Number	E66A06002M010
--------------------	---------------

Reference - Drawing Numbers

Sales Drawing	1201080004-000, SD-120108-094-001
---------------	-----------------------------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_UKCA

- Declaration of

Conformity

China RoHS

Green Image

Not Relevant

Not Contained

CER_4000410542_00_000.pdf

Search Parts in this Series

120108 Series

This document was generated on 09/14/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION