

# MPMP ARCA 3030

**FIBOX**  
Enclosing innovations



Sample image

**Order symbol:** MPMP ARCA 3030

**Product nbr:** 8120921

**Description :** Mounting plate  
multiperforated (250x250x2 mm -  
ø3.6 mm)

**Remarks :** Galvanized steel. for size  
300x300x210

**Including :**

**EAN:** 6418074089489

**El. number:**

- Finland: 3424535
- Denmark:
- Sweden:

| Dimensions: | Length | Width | Height |
|-------------|--------|-------|--------|
| mm:         |        | 250   | 250    |
| inch:       |        | 9.84  | 9.84   |

Materials:

Material:

Base colour:

Cover colour:

Gasket material:

Temperatures:

Temperature °C (short term)::

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation:Not insulated

Halogen free (DIN/VDE 0472, Part 815):0

UV resistance:-

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C:

NEMA Class

Certificates: