

## **BU-12ZXXX-PGX**

(M12 Field Wireable Connectors)



- Mueller's line of M12 field wireable connectors come in a wide variety of configurations.
- Utilizes a quick screw in connection for wires.
- Keyway A Coding
- Both male and female are offered in straight or right-angle orientations.
- Offered in two different threads
  - PG7: Accepts cable diameters between 4.0-6.0mm
  - PG9: Accepts cable diameters between 6.0-8.0mm
- Material:
  - Coupling Nuts Nickel Plated Brass
  - Pins/Contacts Gold Plated Brass
- Ratings:
  - o Current: 4 A
  - Voltage:
    - 3/4-Pin 250V AC/DC
    - 5-Pin 60V
  - Temperature: -25°C to 85°C
- Meets Standard: IEC 61076-2-101
- Protection Class: IEC IP67
- RoHS 3 Compliant

Mueller Electric Company 2850 Gilchrist Rd. Bld 5A Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629 Phone: 330.780.2525 Fax: 330.780.2524

| PART NUMBER   BU-12ZU01-PG7   BU-12ZU02-PG7   BU-12ZU02 PG7 | BODY MATERIAL      | MALE/FEMALE | ORIENTATION        | PIN COUNT | TUDEAD      |
|---|--------------------|-------------|--------------------|-----------|-------------|
| BU-12ZU02-PG7   |                    |             | ONENTATION         |           | THREAD SIZE |
|   | NYLON 66           | MALE        | STRAIGHT           | 3         | PG7         |
|   | NYLON 66           | FEMALE      | STRAIGHT           | 3         | PG7         |
| BU-12ZU03-PG7   | NYLON 66           | MALE        | STRAIGHT           | 4         | PG7         |
| BU-12ZU04-PG7   | NYLON 66           | FEMALE      | STRAIGHT           | 4         | PG7         |
| BU-12ZU05-PG7   | NYLON 66           | MALE        | STRAIGHT           | 5         | PG7         |
| BU-12ZU06-PG7   | NYLON 66           | FEMALE      | STRAIGHT           | 5         | PG7         |
| BU-12ZU21-PG7   | NYLON 66           | MALE        | <b>RIGHT-ANGLE</b> | 3         | PG7         |
| BU-12ZU22-PG7   | NYLON 66           | FEMALE      | <b>RIGHT-ANGLE</b> | 3         | PG7         |
| BU-12ZU23-PG7   | NYLON 66           | MALE        | <b>RIGHT-ANGLE</b> | 4         | PG7         |
| BU-12ZU24-PG7   | NYLON 66           | FEMALE      | <b>RIGHT-ANGLE</b> | 4         | PG7         |
| BU-12ZU25-PG7   | NYLON 66           | MALE        | <b>RIGHT-ANGLE</b> | 5         | PG7         |
| BU-12ZU26-PG7   | NYLON 66           | FEMALE      | <b>RIGHT-ANGLE</b> | 5         | PG7         |
| BU-12ZU01-PG9   | NYLON 66           | MALE        | STRAIGHT           | 3         | PG9         |
| BU-12ZU02-PG9   | NYLON 66           | FEMALE      | STRAIGHT           | 3         | PG9         |
| BU-12ZU03-PG9   | NYLON 66           | MALE        | STRAIGHT           | 4         | PG9         |
| BU-12ZU04-PG9   | NYLON 66           | FEMALE      | STRAIGHT           | 4         | PG9         |
| BU-12ZU05-PG9   | NYLON 66           | MALE        | STRAIGHT           | 5         | PG9         |
| BU-12ZU06-PG9   | NYLON 66           | FEMALE      | STRAIGHT           | 5         | PG9         |
| BU-12ZU21-PG9   | NYLON 66           | MALE        | <b>RIGHT-ANGLE</b> | 3         | PG9         |
| BU-12ZU22-PG9   | NYLON 66           | FEMALE      | <b>RIGHT-ANGLE</b> | 3         | PG9         |
| BU-12ZU23-PG9   | NYLON 66           | MALE        | <b>RIGHT-ANGLE</b> | 4         | PG9         |
| BU-12ZU24-PG9   | NYLON 66           | FEMALE      | <b>RIGHT-ANGLE</b> | 4         | PG9         |
| BU-12ZU25-PG9   | NYLON 66           | MALE        | <b>RIGHT-ANGLE</b> | 5         | PG9         |
| BU-12ZU26-PG9   | NYLON 66           | FEMALE      | <b>RIGHT-ANGLE</b> | 5         | PG9         |
| BU-12ZS31-PG7 N   | ICKEL-PLATED BRASS | MALE        | STRAIGHT           | 3         | PG7         |
| BU-12ZS32-PG7 N   | ICKEL-PLATED BRASS | FEMALE      | STRAIGHT           | 3         | PG7         |
| BU-12ZS33-PG7 N   | ICKEL-PLATED BRASS | MALE        | STRAIGHT           | 4         | PG7         |
| BU-12ZS34-PG7 N   | ICKEL-PLATED BRASS | FEMALE      | STRAIGHT           | 4         | PG7         |
| BU-12ZS35-PG7 N   | ICKEL-PLATED BRASS | MALE        | STRAIGHT           | 5         | PG7         |
| BU-12ZS36-PG7 N   | ICKEL-PLATED BRASS | FEMALE      | STRAIGHT           | 5         | PG7         |
| BU-12ZS41-PG7 N   | ICKEL-PLATED BRASS | MALE        | <b>RIGHT-ANGLE</b> | 3         | PG7         |
| BU-12ZS42-PG7 N   | ICKEL-PLATED BRASS | FEMALE      | <b>RIGHT-ANGLE</b> | 3         | PG7         |
| BU-12ZS43-PG7 N   | ICKEL-PLATED BRASS | MALE        | <b>RIGHT-ANGLE</b> | 4         | PG7         |
| BU-12ZS44-PG7 N   | ICKEL-PLATED BRASS | FEMALE      | <b>RIGHT-ANGLE</b> | 4         | PG7         |
| BU-12ZS45-PG7 N   | ICKEL-PLATED BRASS | MALE        | <b>RIGHT-ANGLE</b> | 5         | PG7         |
| BU-12ZS46-PG7 N   | ICKEL-PLATED BRASS | FEMALE      | <b>RIGHT-ANGLE</b> | 5         | PG7         |
| BU-12ZS31-PG9 N   | ICKEL-PLATED BRASS | MALE        | STRAIGHT           | 3         | PG9         |
|   | ICKEL-PLATED BRASS | FEMALE      | STRAIGHT           | 3         | PG9         |
| BU-12ZS33-PG9 N   | ICKEL-PLATED BRASS | MALE        | STRAIGHT           | 4         | PG9         |
|   | ICKEL-PLATED BRASS | FEMALE      | STRAIGHT           | 4         | PG9         |
| BU-12ZS35-PG9 N   | ICKEL-PLATED BRASS | MALE        | STRAIGHT           | 5         | PG9         |
| BU-12ZS36-PG9 N   | ICKEL-PLATED BRASS | FEMALE      | STRAIGHT           | 5         | PG9         |
| BU-12ZS41-PG9 N   | ICKEL-PLATED BRASS | MALE        | <b>RIGHT-ANGLE</b> | 3         | PG9         |
|   | ICKEL-PLATED BRASS | FEMALE      | <b>RIGHT-ANGLE</b> | 3         | PG9         |
| BU-12ZS43-PG9 N   | ICKEL-PLATED BRASS | MALE        | <b>RIGHT-ANGLE</b> | 4         | PG9         |
| BU-12ZS44-PG9 N   | ICKEL-PLATED BRASS | FEMALE      | <b>RIGHT-ANGLE</b> | 4         | PG9         |
| BU-12ZS45-PG9 N   | ICKEL-PLATED BRASS | MALE        | <b>RIGHT-ANGLE</b> | 5         | PG9         |
|   | ICKEL-PLATED BRASS | FEMALE      | <b>RIGHT-ANGLE</b> | 5         | PG9         |

Mueller Electric Company 2850 Gilchrist Rd. Bld 5A Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629 Phone: 330.780.2525 Fax: 330.780.2524