

Hot-melt glue applicator

Gluematic 3002

Folding box

EAN 4007841 333317

Article number 333317



Ø 11 mm

Glue sticks



CE



VDE

Function description

One for almost all. Hot-glue melt applicator Gluematic 3002, for hobby and trade use, high delivery rate of 16 g/min, small and practical, heating-up time of just 7 minutes, interchangeable nozzles.

Technical specifications

Output	45 W	Temperature, adjustable	No
Temperature	206 °C	Heating element	PTC heating element
Warm-up time	7 min	Voltage range (min)	100 V
Delivery rate	16 gr/min	Suitable for	Glass, Rubber, Wood, ceramic, Leather, Paper, Card / cardboard boxes, PP, Textiles
Max. stick diameter	11 mm	Cord length	2 m
Function, hanger	No	Dimensions (L x W x H)	185 x 30 x 160 mm
Soft grip	No	Version	Folding box
Idle mode	No	PU1, net weight	0,317 kg
Nozzle can be changed	Yes	Manufacturer's Warranty	3 years
Stroke adjustment	No	PU1, EAN	4007841333317

Accessories

EAN 4007841 076061	Standard 2 mm nozzle for Gluematic 3002 / 5000
EAN 4007841 075965	Long nozzle 2.8 mm for Gluematic 3002 / 5000
EAN 4007841 076160	Fine nozzle 1.0 mm for Gluematic 3002 / 5000
EAN 4007841 048419	Glue sticks Ø 11 mm Crystal

<https://www.steinell.de>

Subject to technical modifications

11.2022 Page 1 from 2

Hot-melt glue applicator

Gluematic 3002

Folding box

EAN 4007841 333317

Article number 333317



Accessories

EAN 4007841 044930	Glue sticks, Ø 11 mm Ultra-Power
EAN 4007841 006815	Color sticks Ø 11 mm
EAN 4007841 064891	Glitter Sticks Ø 11 mm
EAN 4007841 006808	Glue sticks Ø 11 mm white
EAN 4007841 006792	Glue sticks Ø 11 mm black
EAN 4007841 006778	Glue sticks Ø 11 mm wood