

Model		PSUIP 1X4A 24VAC
Input Range		AC 220V rated 3Amp main fuse
Input Frequency		50Hz
Output Current		1 x 4A
Output Voltage		24VAC
Fuse		Auto-reset PTC Fuse for each output, rated 5Amp
Surge Protected		Yes
Weight		2.8kg
Case Type		Grey Polycarbonate
Operating Temp		- 10°C to 40°C
Storage Temp		- 20°C to +50°C
Operating Humidity		0% to 95% RH non condensing
Size		15cmx27cmx8.9cm (WxHxD)
IP Rating (when correctly installed)		IP66

