

Series TC 44 18

Panel Mount 2 Row Barrier Terminal Block



4 Ways shown, various available

Housing	PA66, UL94V-0
Screws	M3.5 Steel Nickel plated
Terminals	Copper alloy, Tin plated
Temperature Range	-40°C ~ +105°C
Standard	CE (BS EN 60998)
Current Rating	20 A
Voltage Rating	300 V
Withstanding Voltage	AC 2000V / 1 Min
Insulation Resistance	500 MΩ / DC 500V
Contact Resistance	20 mΩ
Wire Range	22-12AWG
Torque	0.8Nm

See Product Page for Diagram & Dimensions :

www.thermodatacomponents.co.uk/2rowbarrier