

## **Product data sheet**

## 610 286 3

## Ferrule crimping tool PEW 8.286

Sideways insertion



- For crimping insulated and non-insulated wire-end ferrules according to DIN 46 228
- Self-adjusting adaptation to the required size of wire-end ferrule
- Wire-end ferrules are inserted sideways into the tool
- Force magnified by lever action to ensure fatigue-free working
- Precise, factory-set (calibrated) crimping pressure
- Consistent crimping quality with forced-lock completion of crimping process (can be released)
- Black-oxide finish
- Specially hardened spring steel
- Ergonomic 2-component grips

General	
Item number	610 286 3
EAN	4049002150746
Weight	417 g
Dimension	180 mm
Dimension packaging	250 x 108 x 43 mm

Specifications	
Finish	black-oxide finish
Grips	2-component grips
Range of applications	Ferrules
Capacity	0.08 – 16.0 mm² / AWG 28 – 6
Twin wire-end ferrules	2x 0.25 – 10.0 mm² / 2x AWG 22 – 8

Classification	
eCl@ss 10.1	ACD215012
ETIM 7.0	EC000168
proficl@ss 7.0	AAA946c003

With reservations regarding technical modifications and errors. Illustration may vary.