

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [112115001](#)

Status: **Active**

Overview: [Industrial Ethernet Switches](#)

Description: Direct-Link Industrial 5-Port, IP67 (Machine Mount) Ethernet Switch, Unmanaged, 5-pole M12 Ultra-Lock, 10/100 Mb/s

General

| | |
|----------------------|--|
| Product Family | Switches |
| Series | 112111 |
| Approvals | CE certified, UL (pending) |
| Comments | 2.0W (24VDC) |
| IP Rating | IP67 |
| MAC Address | N/A |
| Overview | Industrial Ethernet Switches |
| Product Name | Direct-Link |
| Protocol | EtherNet (IEEE 802.3) |
| Switch Functionality | Unmanaged |
| Taxonomy | Industrial Ethernet Switches |
| UPC | 883906689483 |

Physical

| | |
|-------------------------------|-------------------------------|
| Ethernet Connector | 4-Pole Ultra-Lock® (M12) Conn |
| Housing Width | 30.00mm |
| Mechanical Shock | 50G (IEC 68-2-29) |
| Mounting Style | N/A |
| Net Weight | 0.220/kg |
| Packaging Type | Carton |
| Ports | 5 |
| Power Input | 5-pole Micro-Change (M12) |
| Temperature Range - Operating | -40° to +75°C |
| Uplink Connection | 5-Pole Micro-Change (M12) |
| Vibration | 7g (IEC 68-2-29) |

Electrical

| | |
|--------------------------|--|
| Current - Maximum Output | N/A |
| EMC | EN 61000-4-2, EN 61000-4-4, EN 61000-4-5, EN 61326 |
| Supply Voltage | 2.0W (24V DC) |

Material Info

| | |
|--------------------|---------|
| Engineering Number | DRL-750 |
|--------------------|---------|

Reference - Drawing Numbers

| | |
|---------------|---------------|
| Sales Drawing | 112115001-000 |
|---------------|---------------|

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 7(a),7(c)-I,6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[112111](#) Series