

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1211290084](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN NBR Profiled Gasket, Form B-10mm and Form B-11mm, 1 Bag of 100

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	121129
Form	B - 11mm
IP Rating	IP65, IP67
Material - Contact	N/A
Overview	mPm DIN Valve Connectors
Product Name	mPm
Taxonomy	Circular Industrial Connectors
Type	Field Attachable Connector
UPC	78678837667

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	NBR
Material - Coupling Nut	N/A
Material - Plating Mating	n/a
Net Weight	154.200/g
Orientation	N/A
Pitch - Mating Interface	N/A
Poles	N/A
Temperature Range - Operating	N/A
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	N/A

Material Info

Engineering Number	3011-07
--------------------	---------

Reference - Drawing Numbers

Sales Drawing	SD-121129-084-001
---------------	-------------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

ZZCERT_UKCA

- Declaration of

Conformity

China RoHS

Green Image

Not Relevant

Not Contained

CER_4000428676_00_000.pdf

CER_4000428678_00_000.pdf

Search Parts in this Series

121129 Series