



MHF4 Pigtail Cables

I-PEX MHF4 To SMA Female Bulkhead Jack 1.13 Coax Cable



Applications

- SMA Female to MHF-4 jumper cable
- RF connections for radios and antennas
- MHF4 LK ideal for continuous shock & vibration applications

Attenuation

Frequency (GHz)	1 GHz	2 GHz	3 GHz	4 GHz	5 GHz	6 GHz
dB 1/m	2.2	3.1	3.9	4.5	5.0	5.5

Key Features

- Low Loss coaxial cable
- OD 1.13mm
- Color Grey
- Various cable lengths available
- RoHS and REACH compliant
- Crimp strength 20N minimum
- MHF4 locking solution available

Electrical Specifications

Suggested working frequency:	0 to 6 GHz		
Nominal Impedance:	50 +/- 3 Ω		
Maximum operating voltage:	30 V		
VSWR:	-15 dB (Max. between 0 and 6 GHz)		

Environmental Specifications

Operating Temperature:	-20 to +60 °C
Storage Temperature:	-20 to +60 °C
RoHS Compliant:	YES
REACH Compliant:	YES






MHF4 Pigtail Cables

I-PEX MHF4 To SMA Female Bulkhead Jack 1.13 Coax Cable


Mechanical Drawing

Note: The O-ring is applicable to the IP67 models.




Cable length (See page 3)


RECOMMENDED MOUNTING HOLE



MHF 4L LK PLUG 3:1



MHF 4L PLUG 8:1







MHF4 Pigtail Cables

I-PEX MHF4 To SMA Female Bulkhead Jack 1.13 Coax Cable

Mechanical Specifications

Product	Length (mm)	Description	Connector 1	Connector 2	Mounting Type	
ASMGA003XB113S11	30		I-PEX/MHF4			
ASMGA005XB113S11	50				REAR MOUNT	
ASMGA0075XB113S11	75					
ASMGA010XB113S11	100	1				
ASMGA0125XB113S11	125					
ASMGA015XB113S11	150	L DEVANUEATO CAMA ESMALE DUILIZUEAD 4.40 CADLE				
ASMGA003XA113S11	30	I-PEX MHF4 TO SMA FEMALE BULKHEAD 1.13 CABLE			FRONT MOUNT	
ASMGA005XA113S11	50					
ASMGA0075XA113S11	75					
ASMGA010XA113S11	100					
ASMGA0125XA113S11	125					
ASMGA015XA113S11	150					
ASMGA003XD113S11	30			SMAF BLKHD	REAR MOUNT	
ASMGA005XD113S11	50		IP67/I-PEX/MHF4			
ASMGA0075XD113S11	75					
ASMGA010XD113S11	100					
ASMGA0125XD113S11	125					
ASMGA015XD113S11	150	IP67 I-PEX MHF4 TO SMA FEMALE BULKHEAD 1.13 CABLE				
ASMGA003XC113S11	30	1F07 1-FEX WITH TO SWIA FEWALE BULKHEAD 1.13 CABLE			FRONT MOUNT	
ASMGA005XC113S11	50					
ASMGA0075XC113S11	75					
ASMGA010XC113S11	100					
ASMGA0125XC113S11	125					
ASMGA015XC113S11	150					
ASMGAL010XC113S11	100	IP67 I-PEX MHF4 LK TO SMA FEMALE BULKHEAD 1.13 CABLE	IP67/I-PEX/MHF4 LK]	REAR MOUNT/LOCKING MECHANISM	
ASMGLKL010XC137S11	100	IP67 I-PEX MHF LK TO SMA FEMALE BULKHEAD 1.13 CABLE	IP67/I-PEX/MHF LK		REAR MOUNT/LOCKING MECHANISM	