D-Sub Connectors and Backshells Multicomp PRO



RoHS **Compliant**







D-Sub Connector with Backshell

Backshell

Features

- Available in sizes 9, 15, 25 and 37
- Minimise interference from electromagnetic and RF sources
- Non-static parts avoid ESD problems
- Accept round foil and braided cable types
- Approved according VDE 0871, FCC 20780 and 89/336/EU
- Long Jackscrews with UNC 4-40 Thread as Standard
- No special assembly tools required

Specifications

Backshell

Material : ABS, Ni-plated Temperature Range : -40°C to 105°C

Cable Strain Relief : Polycarbonate, PC UL94 V0

Cable Diameter : 3mm to 13mm

Locking Screws : Long jackscrews UNC 4-40

Jackscrew Colour : Black Assembly Screws : Self tapping Cable Outlet : Straight

Attenuation Factor : > 40 dB between 30 MHz and 1GHz

D-Sub Solder Connector

Insulator : PBT, UL94 V-0 Shell : Steel, Tin-plated **Contact Pins** : Copper alloy

Contact Plating : Selective Gold over Nickel

Temperature Range : -55°C to +105°C

Insulator Resistance : 1000M Withstand Voltage : 1kV for 1 min

Stamped Contacts : Class 3, 100 inserts minimum


Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



D-Sub Connectors and Backshells Multicomp PRO



Diagram



| Part Number | Α | В |
|-------------|------|------|
| MP002016 | 31 | 38.3 |
| MP002017 | 39.3 | 40.5 |
| MP002018 | 53 | 47.8 |
| MP002019 | 69.5 | 52.2 |
| MP002040 | 31 | 38.3 |
| MP002041 | 31 | 38.3 |
| MP002042 | 39.3 | 40.5 |
| MP002043 | 39.3 | 40.5 |
| MP002044 | 53 | 47.8 |
| MP002045 | 53 | 47.8 |
| MP002046 | 69.5 | 52.2 |
| MP002047 | 69.5 | 52.2 |

Part Number Table

| Description | Part Number |
|---|-------------|
| D Sub Backshell, Metalized Plastic, DE-9, Straight | MP002016 |
| D Sub Backshell, Metalized Plastic, DA-15, Straight | MP002017 |
| D Sub Backshell, Metalized Plastic, DB-25, Straight | MP002018 |
| D Sub Backshell, Metalized Plastic, DC-37, Straight | MP002019 |
| D Sub Connector with Backshell, DE-9, Straight, Female | MP002040 |
| D Sub Connector with Backshell, DE-9, Straight, Male | MP002041 |
| D Sub Connector with Backshell, DA-15, Straight, Female | MP002042 |
| D Sub Connector with Backshell, DA-15, Straight, Male | MP002043 |
| D Sub Connector with Backshell, DB-25, Straight, Female | MP002044 |
| D Sub Connector with Backshell, DB-25, Straight, Male | MP002045 |
| D Sub Connector with Backshell, DC-37, Straight, Female | MP002046 |
| D Sub Connector with Backshell, DC-37, Straight, Male | MP002047 |

Dimensions : Millimetres

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

