

GRM31B5C3A681FWA1L

“#” indicates a package specification code.



< List of part numbers with package codes >

GRM31B5C3A681FWA1L GRM31B5C3A681FWA1K

Appearance & Shape



References

Packaging	Specifications	Standard Packing Quantity
L	180Embossed Tape	3000
K	330Embossed Tape	10000

Mass (typ.)	
1 piece	29.0mg
φ180mm Reel	137g

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GRM31B5C3A681FWA1L

“#” indicates a package specification code.



Specifications

Length	3.2±0.2mm
Width	1.6±0.2mm
Thickness	1.25+0/-0.3mm
Capacitance	680pF ±1%
Distance between external terminals g	1.5mm min.
External terminal size e	0.3mm min.
Operating Temperature Range	-55°C to 125°C
Rated Voltage	1000Vdc
Size code in inch(mm)	1206 (3216M)
TC	0±30ppm/°C
Temperature characteristics (complied standard)	C0G(EIA)
Temperature range of temperature characteristics	25°C to 125°C

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.