




C-174253

METRIC

PROP. NO. 94-25979-000

PRINT DIST

PRINT DIST

AMP-J010-2C
REV. 3/93SECT. "A"- "A"
(SCALE: 4-1)

NOTE.

1. MATERIAL

- (1) HOUSING: GLASS FILLED THERMOPLASTIC, GRAY (UL94V-0)
 - (2) CONTACTS: COPPER ALLOY
FINISH: CONTACT AREA, 0.0002 MIN. Au PLATING OVER Ni UNDER PLATING.
SOLDERING AREA, TIN-LEAD PLATING OVER Ni UNDER PLATING.
 - (3) RETENTION-LEG: COPPER ALLOY
FINISH: TIN-LEAD PLATING OVER Ni UNDER PLATING.
- △ GROUND CONTACTS: ON NO.1 & 16 (2 PL.) IN ROW b.

注記 1. 材料

- (1) ハウジング: ガラス入り熱可塑性樹脂, 灰色 (UL94V-0)
 - (2) コンタクト: 銅合金 仕上げ: ニッケル下地めっき
接触部: 金めっき 0.2µm以上
タイン: 半田めっき
 - (3) リテンションレグ: 銅合金 仕上げ: ニッケル下地めっき, 半田めっき
- △ グランドコンタクト: b列 NO.1, 16 (2箇所) に配置。

Copyright ©1994年 日本エー・エム・ピー株式会社		Copyright ©1994 AMP (Japan), LTD. ALL RIGHTS RESERVED.		AMP 日本エー・エム・ピー株式会社 Tokyo, Japan	
電線径範囲 (WIRE RANGE) mm ² (AWG -)		絶縁外径 (INSULATION DIA.) mmφ		名称 (NAME) DR DIN CONN. FEMALE (WITH GROUND AND R-LEG)	
材料 (MATERIAL) SEE NOTE		仕上 (FINISH) SEE NOTE		一般公差 (GENERAL TOLERANCE) 10以下: ±0.2 10以上 30以下: ±0.25 30以上 100以下: ±0.3 角 度: ±3°	
DR. S. HASHIMOTO S. HASHIMOTO 6-JAN-95		DE. S. Hashimoto S. Hashimoto 6-JAN-95		LOC. J 番号 (No.) C-174253	
LIT. 変更 (REVISION RECORD)		DR. CHK. DATE		尺度 (SCALE) 2-1 REV. E SHEET 2 OF 2	

(CUSTOMER DRAWING) 参 考 図 面