

GJM0335G2A8R7WB01D

“#” indicates a package specification code.



< List of part numbers with package codes >

GJM0335G2A8R7WB01D

GJM0335G2A8R7WB01W

GJM0335G2A8R7WB01J

Appearance & Shape



References

| Packaging | Specifications | Standard Packing Quantity |
|-----------|-------------------------|---------------------------|
| D | 180mm Paper Tape | 15000 |
| W | 180mm Paper Tape (W8P1) | 30000 |
| J | 330mm Paper Tape | 50000 |

| Mass (typ.) | |
|-------------|--------|
| 1 piece | 0.33mg |
| φ180mm Reel | 118g |

Attention

- This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GJM0335G2A8R7WB01D

“#” indicates a package specification code.



Specifications

| | |
|--|----------------|
| Length | 0.6±0.03mm |
| Width | 0.3±0.03mm |
| Thickness | 0.3±0.03mm |
| Capacitance | 8.7pF ±0.05pF |
| Distance between external terminals g | 0.2mm min. |
| External terminal size e | 0.1 to 0.2mm |
| Operating Temperature Range | -55°C to 150°C |
| Rated Voltage | 100Vdc |
| Size code in inch(mm) | 0201 (0603M) |
| TC | 0±30ppm/°C |
| Temperature characteristics (complied standard) | -(Murata) |
| Temperature range of temperature characteristics | 25°C to 150°C |

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.