

ZRB186R60G226ME11L


“#” indicates a package specification code.



< List of part numbers with package codes >

ZRB186R60G226ME11L ZRB186R60G226ME11K

Appearance & Shape



References

Packaging	Specifications	Standard Packing Quantity
L	180Embossed Tape	4000
K	330Embossed Tape	10000

Mass (typ.)	
1 piece	8.6mg
φ180mm Reel	81g

Notices

Only for mobile devices. Measure capacitance after heat treatment

Attention

- This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

ZRB186R60G226ME11L

“#” indicates a package specification code.



Specifications

Length	1.6±0.22mm
Width	0.8±0.2mm
Thickness	0.6±0.2mm
Capacitance	22µF ±20%
Distance between external terminals g	0.6mm min.
External terminal size e	0.2 to 0.65mm
Operating Temperature Range	-55°C to 85°C
Rated Voltage	4Vdc
Size code in inch(mm)	0603 (1608M)
Capacitance change rate	±15.0%
Temperature characteristics (complied standard)	X5R(EIA)
Temperature range of temperature characteristics	-55°C to 85°C

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.