



infrastructure for a connected world

## PRODUCT CHANGE NOTIFICATION

Product Category STRONGHOLD **20221011-1**

Product Group STRONGHOLD

ISSUE DATE: ☒ NA ☒ EMEA ☒ LATAM ☒ AP1-Oct-22

IMPACTED REGIONS: ☐ DISCONTINUATION

REASON FOR CHANGE: ☒ OTHER

### DESCRIPTION OF CHANGE: (Required)

The country of origin is changing for Stronghold Terminals from Mexico to Taiwan. All parts are direct replacements. No parts are being discontinued.

Photos/Drawing (where applicable)

IMPACTED PART NUMBERS AND REPLACEMENT PART NUMBERS: (where applicable)

[Reference Page 2 / Linked PDF](#)

**DATES: DISCONTINUATION AND NEW PRODUCT AVAILABILITY:**

| SCHEDULE FOR CHANGE                  | Year<br>(YYYY) | Month<br>(MM) | Day<br>(DD) |
|--------------------------------------|----------------|---------------|-------------|
| New product sample availability date |                |               |             |
| Old product discontinuation date*    |                |               |             |

**CUSTOMER SERVICE CONTACTS**

|               |                                                                                                                                                      |                                                                                                                                                        |                                                                                                                                         |
|---------------|------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| ASIA PACIFIC  | AUSTRALIA: 1-800 7263848<br><a href="mailto:AUS-CSVM@panduit.com">AUS-CSVM@panduit.com</a>                                                           | CHINA: 400-820-1900<br><a href="mailto:CHN-CustomerService@panduit.com">CHN-CustomerService@panduit.com</a>                                            | HONG KONG: 800-965768<br><a href="mailto:CHN-CustomerService@panduit.com">CHN-CustomerService@panduit.com</a>                           |
|               | INDIA: 000 800 6501844 (Fixed)<br>000 800 6500369 (Mobile)<br><a href="mailto:SGP-Customer_Service@panduit.com">SGP-Customer_Service@panduit.com</a> | INDONESIA: 001 803 65 7571<br><a href="mailto:SGP-Customer_Service@panduit.com">SGP-Customer_Service@panduit.com</a>                                   | JAPAN: +81-3-6863-6000<br><a href="mailto:JPN-CS@panduit.com">JPN-CS@panduit.com</a>                                                    |
|               | KOREA: 02-2182-7300<br><a href="mailto:KOR-CustomerService@panduit.com">KOR-CustomerService@panduit.com</a>                                          | MALAYSIA 1800 801435<br><a href="mailto:SGP-Customer_Service@panduit.com">SGP-Customer_Service@panduit.com</a>                                         | SINGAPORE: 1-800-7263848<br><a href="mailto:SGP-Customer_Service@panduit.com">SGP-Customer_Service@panduit.com</a>                      |
|               | TAIWAN: 0080 165 1487<br><a href="mailto:SGP-Customer_Service@panduit.com">SGP-Customer_Service@panduit.com</a>                                      | THAILAND: 001-800-65-6385<br><a href="mailto:SGP-Customer_Service@panduit.com">SGP-Customer_Service@panduit.com</a>                                    |                                                                                                                                         |
| LATIN AMERICA | BRAZIL 08000562613 (Toll Free)<br><a href="mailto:BRA-custservice@panduit.com">BRA-custservice@panduit.com</a>                                       | MEXICO: +52-33-37776000 x80520<br>01 800 360 86 00 (Toll Free)<br><a href="mailto:MEX-customerservice@panduit.com">MEX-customerservice@panduit.com</a> | OTHER LA COUNTRIES:<br>Phone USA 1-708-532-1800<br><a href="mailto:TP-CS-INTERNATIONAL@panduit.com">TP-CS-INTERNATIONAL@panduit.com</a> |
| NORTH AMERICA | USA & CANADA: 1-800-777-3300<br><a href="mailto:cs@panduit.com">cs@panduit.com</a>                                                                   | EMEA                                                                                                                                                   | EMEA: +44 208 6017219<br><a href="mailto:EMEA-CustomerServices@panduit.com">EMEA-CustomerServices@panduit.com</a>                       |

To add a contact or to unsubscribe, please send an email to:

[PCN@panduit.com](mailto:PCN@panduit.com)

| <b>IMPACTED PART<br/>NUMBER(s)</b> | <b>Replacement Part</b> |
|------------------------------------|-------------------------|
| EDNF10250FIMB-Q                    | EDNF10250FIMBKQ         |
| EDNF10-250FI-Q                     | EDNF10-250FIKQ          |
| EDNF14-188FIB-Q                    | EDNF14-188FIBKQ         |
| EDNF14-250FIB-L                    | EDNF14-250FIBKL         |
| EDNF14-250FIB-Q                    | EDNF14-250FIBKQ         |
| EDNF14250FIMB-L                    | EDNF14250FIMBKL         |
| EDNF14250FIMB-Q                    | EDNF14250FIMBKQ         |
| EDNF18-188FIB-L                    | EDNF18-188FIBKL         |
| EDNF18-188FIB-Q                    | EDNF18-188FIBKQ         |
| EDNF18-250FIB-L                    | EDNF18-250FIBKL         |
| EDNF18-250FIB-Q                    | EDNF18-250FIBKQ         |
| EDNF18250FIMB-L                    | EDNF18250FIMBKL         |
| EDNF18250FIMB-Q                    | EDNF18250FIMBKQ         |
| EDV10-250M-Q                       | EDV10-250MK-Q           |
| EDV10-250-Q                        | EDV10-250K-Q            |
| EDV14-250B-L                       | EDV14-250BK-L           |
| EDV14-250B-Q                       | EDV14-250BK-Q           |
| EDV14-250M-L                       | EDV14-250MK-L           |
| EDV14-250M-Q                       | EDV14-250MK-Q           |
| EDV14-250P-LYY                     | EDV14-250PK-LYY         |
| EDV18-250B-L                       | EDV18-250BK-L           |
| EDV18-250B-Q                       | EDV18-250BK-Q           |
| EDV18-250M-L                       | EDV18-250MK-L           |
| EDV18-250M-Q                       | EDV18-250MK-Q           |
| EDV18-250P-LYY                     | EDV18-250PK-LYY         |
| EJN218-216-L                       | EJN218-216K-L           |
| EJN218-216-Q                       | EJN218-216K-Q           |
| EJN314-412-Q                       | EJN314-412K-Q           |

|              |               |
|--------------|---------------|
| EJN418-212-Q | EJN418-212K-Q |
| ESV10BX-Q    | ESV10BXK-Q    |
| ESV14BX-L    | ESV14BXK-L    |
| ESV14BX-Q    | ESV14BXK-Q    |
| ESV18BX-L    | ESV18BXK-L    |
| ESV18BX-Q    | ESV18BXK-Q    |
| EV10-10FB-D  | EV10-10FBK-D  |
| EV10-10FB-Q  | EV10-10FBK-Q  |
| EV10-10LFB-Q | EV10-10LFBK-Q |
| EV10-10RB-D  | EV10-10RBK-D  |
| EV10-10RB-Q  | EV10-10RBK-Q  |
| EV10-14FB-Q  | EV10-14FBK-Q  |
| EV10-14LFB-Q | EV10-14LFBK-Q |
| EV10-14RB-D  | EV10-14RBK-D  |
| EV10-14RB-Q  | EV10-14RBK-Q  |
| EV10-38RB-Q  | EV10-38RBK-Q  |
| EV10-56RB-Q  | EV10-56RBK-Q  |
| EV10-6FB-Q   | EV10-6FBK-Q   |
| EV10-6LFB-Q  | EV10-6LFBK-Q  |
| EV10-6RB-Q   | EV10-6RBK-Q   |
| EV10-8FB-D   | EV10-8FBK-D   |
| EV10-8FB-Q   | EV10-8FBK-Q   |
| EV10-8LFB-Q  | EV10-8LFBK-Q  |
| EV10-8RB-D   | EV10-8RBK-D   |
| EV10-8RB-Q   | EV10-8RBK-Q   |
| EV10-P55-QYY | EV10-P55K-QYY |
| EV14-10FB-L  | EV14-10FBK-L  |
| EV14-10FB-M  | EV14-10FBK-M  |
| EV14-10FB-Q  | EV14-10FBK-Q  |
| EV14-10LFB-L | EV14-10LFBK-L |

|              |               |
|--------------|---------------|
| EV14-10LFB-Q | EV14-10LFBK-Q |
| EV14-10RB-L  | EV14-10RBK-L  |
| EV14-10RB-M  | EV14-10RBK-M  |
| EV14-10RB-Q  | EV14-10RBK-Q  |
| EV14-14RB-L  | EV14-14RBK-L  |
| EV14-14RB-M  | EV14-14RBK-M  |
| EV14-14RB-Q  | EV14-14RBK-Q  |
| EV14-6FB-L   | EV14-6FBK-L   |
| EV14-6FB-Q   | EV14-6FBK-Q   |
| EV14-6LFB-L  | EV14-6LFBK-L  |
| EV14-6LFB-Q  | EV14-6LFBK-Q  |
| EV14-6RB-L   | EV14-6RBK-L   |
| EV14-6RB-Q   | EV14-6RBK-Q   |
| EV14-8FB-L   | EV14-8FBK-L   |
| EV14-8FB-Q   | EV14-8FBK-Q   |
| EV14-8LFB-L  | EV14-8LFBK-L  |
| EV14-8LFB-Q  | EV14-8LFBK-Q  |
| EV14-8RB-L   | EV14-8RBK-L   |
| EV14-8RB-M   | EV14-8RBK-M   |
| EV14-8RB-Q   | EV14-8RBK-Q   |
| EV14-P47B-Q  | EV14-P47BK-Q  |
| EV18-10FB-Q  | EV18-10FBK-Q  |
| EV18-10LFB-L | EV18-10LFBK-L |
| EV18-10RB-L  | EV18-10RBK-L  |
| EV18-10RB-Q  | EV18-10RBK-Q  |
| EV18-14RB-L  | EV18-14RBK-L  |
| EV18-14RB-Q  | EV18-14RBK-Q  |
| EV18-6FB-L   | EV18-6FBK-L   |
| EV18-6FB-Q   | EV18-6FBK-Q   |
| EV18-6LFB-L  | EV18-6LFBK-L  |

|             |              |
|-------------|--------------|
| EV18-6LFB-Q | EV18-6LFBK-Q |
| EV18-6RB-L  | EV18-6RBK-L  |
| EV18-6RB-Q  | EV18-6RBK-Q  |
| EV18-8FB-L  | EV18-8FBK-L  |
| EV18-8FB-M  | EV18-8FBK-M  |
| EV18-8FB-Q  | EV18-8FBK-Q  |
| EV18-8LFB-Q | EV18-8LFBK-Q |
| EV18-8RB-L  | EV18-8RBK-L  |
| EV18-8RB-Q  | EV18-8RBK-Q  |
| EV18-P47B-L | EV18-P47BK-L |