

## Coaxial Panel Connector 23\_SMA-50-0-21/111\_N

### Description

Straight panel receptacle jack, flange mount

Interface standards

IEC 60169-15\_MIL-STD-348A/310\_CECC 22110



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	18 GHz

#### Mechanical Data

Number of matings	500
Weight	0.0026 kg

#### Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

### Related Documents

Catalogue drawing	DCA-00010321
-------------------	--------------

### Ordering Information

Single package	23_SMA-50-0-21/111_NE
----------------	-----------------------