

## Coaxial Panel Connector 22\_N-50-0-3/133\_N

### Description

Straight bulkhead receptacle jack

Interface standards

IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

#### Mechanical Data

Number of matings	500
Weight	0.0465 kg

#### Environmental Data

Operating temperature	-50 °C to 160 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	not compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	Glass Bead	
Gasket	NR (Natural Rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00011059
Catalogue drawing	DCA-00011061

### Ordering Information

Single package	22_N-50-0-3/133_NE
----------------	--------------------

### Remarks

Hermetically sealed: leak rate  $\leq 10^{-6}$  Torr l/s (atm cc/s)