

Data Sheet | Item Number: 207-3308

WAGO Box; Branch; for multicore cables; Capsule; PUSH WIRE®, lever connector; max. 4 mm² connectors; without splicing connectors; for BS 5733 - MF; black



<https://www.wago.com/207-3308>



Color: black

- Quick and easy to install
- Screwless design
- IP68 – Ideal for outdoor applications
- Complies with BS EN 60529 and BS 7671 – Further information: Please, download the product detail data sheet.

Electrical data

Ratings per IEC/EN

Ratings (note)	Rated current: up to 41 A; Rated voltage: 400 V; Rated impulse voltage: 4 kV
----------------	--

Physical data

Width	92 mm / 3.622 inches
Height	122 mm / 4.803 inches
Depth	92 mm / 3.622 inches

Material Data

Note (material data)	Information on material specifications can be found here
Color	black
Fire load	0 MJ
Weight	141.7 g

Commercial data

ETIM 8.0	EC001170
PU (SPU)	1 pcs
GTIN	4055143220958

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product
Compliance 207-3308



Documentation

Additional Information

Technical Section	pdf 2142.18 KB	
207-3308 WAGO Box	pdf 1015.84 KB	