

Coaxial Cable Connector 11_QLA-01-3-2/122_N

Description

Straight cable plug

Interface standards

NIM-CAMAC-Standard CD/N549



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	1.4 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0051 kg

Environmental Data

Operating temperature	-55 °C to 150 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	Nickel Plating
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Catalogue drawing	DOU-00006540
Assembly instruction	DOC-0000180108

Ordering Information

Single package	11_QLA-01-3-2/122_NE
----------------	----------------------

Additional Information

Suitable cables	RG_223_/U, RG_142_B/U
-----------------	-----------------------