

## Coaxial Panel Connector 22\_SHV-50-0-6/133\_N

### Description

Straight bulkhead receptacle jack

Interface standards

IEC 60498\_MIL-STD-348A/314



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	0.3 GHz

#### Mechanical Data

Chassis torque	2 Nm
Number of matings	500
Weight	0.0111 kg

#### Environmental Data

Operating temperature	-55 °C to 100 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PS (Polystyrene)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00011058
Catalogue drawing	DCA-00010449
Mounting hole	DOU-00008762

### Ordering Information

Single package	22_SHV-50-0-6/133_NE
----------------	----------------------