Data Sheet

Coaxial Panel Connector 22_N-50-0-2/133_N

Description

Straight bulkhead receptacle jack

Interface standards IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data Impedance Interface frequency max.	50 Ω 11 GHz
Mechanical Data Number of matings Weight	500 0.0457 kg
Environmental Data Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102)	-65 °C to 165 °C compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Related Documents

Ordering Information

Single package

22_N-50-0-2/133_NE

Remarks

With panel seal

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.

HUBER+SUHNER