

Coaxial Cable Connector 16_N-50-7-31/133_N

Description

Right angle cable plug

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0451 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Brass	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00005990
Catalogue drawing	DOU-00005992
Assembly instruction	DOC-0000179199

Ordering Information

Bulk 100 pcs package	16_N-50-7-31/133_NH
Single package	16_N-50-7-31/133_NE

Additional Information

Suitable cables	RG_214_/U, GX_07272_D, ENVIROFLEX_393, GX_07272_D-04, RADOX_RF_214
-----------------	--